Datasheet for part number TN6LS24-0048S1L

Our Catalog Part Number: TN6LS24-0048S1L
Our Global Manufacturing Part Number: 192991-0648
Brand: Cannon Product Category: Trident Product Line: Trident Series: TN

Product Datasheet	
Series	Trident Neptune
Connector Type	Plug
Environmental Sealing	IP67
Sealing Methode	Large Sealing Grommet and Gland Nut (for thick insulation wires)
Shell Size	24
Contact Quantity	48
Power Contacts	0
Signal Contacts	48
Contact Gender	Socket
Contacts included	No, order separately
Operating Voltage	48 Vac, 60 Vdc
Current Rating	Up to 16 A
Operating Temperature	-55°C to +105°C
Insulator Resistance	5000 Megaohms at 500 V dc
Durability	Up to 500 Mating Cycles
Flammability	UL94-V0
Salt Spray	48 hours
Vibration	10 g's peak, 10 to 500 Hz, 9 hours
Physical Shock	40 g's peak, 6msec., half-sine pulse
Insulator Material	Black Nylon
Coupling Nut Material	Nickel Plated Copper Alloy
Sealing Grommet Material	Silicone Rubber
Packaging	Single Pack
Modification Code	Standard part

Specifications and dimensions subject to change.

Downloaded from Arrow.com.