



Pushing Performance
Since 1945

Han 24HPR VarioShell-2x24HPR-Set0



Image is for illustration purposes only. Please refer to product description.

Part number	10 40 124 1000
Specification	Han 24HPR VarioShell-2x24HPR-Set0
HARTING eCatalogue	https://harting.com/10401241000

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR VarioShell
Type of hood/housing	Complete set
Description of hood/housing	Angled

Version

Size	24 HPR VS
VarioShell level 1	1x 24 B
VarioShell level 2	1x 24 B
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	Please note the installation manual.
Pack contents	Bulkhead mounted housing Mounting cover Fixing screws

Technical characteristics

Tightening torque	4 Nm Mounting cover 12 Nm Fixing screws 12 Nm PE screw
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP66
	IP67
	IP68
	IP69

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR

Specifications and approvals

Specifications	IEC 61984
	IEC 61373 Category 1 Class B
Approvals	CE

Commercial data

Packaging size	1
Net weight	3 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140175587
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466