

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Connector
- ? 2.54 mm Centerline
- ? Number of Positions = 13
- ? Number of Rows = Single
- ? Housing Style = With Mounting Ears

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

 Active

 [Add to Part List](#)

Product Drawings:

[13 positions AMP EDGE connector, 2.54 Pitch single I...](#) (PDF, Italian)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files:

? None Available

Additional Information:

? Product Line Information

Related Products:

? Tooling

List all Documents

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Connector
- ? Number of Positions = 13
- ? Housing Style = With Mounting Ears
- ? Mounting Ear Style = Molded
- ? PCB Mount Angle = Vertical
- ? Post Type = Board to Board
- ? PCB Thickness (mm [in]) = 1.60 [0.063]
- ? Keying Plug Material = Synthetic
- ? Profile = Low

Body Related Features:

? Centerline (mm [in]) = 2.54 [0.100]
 ? Number of Rows = Single

Contact Related Features:

? Contact Mating Area Plating Material = Gold
(15)

? Contact Material = Phosphor Bronze

Housing Related Features:

? Housing Material = Polyester GF

? Housing Color = Green

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

? Brand = AMP