



**Part Number :** [1301370149](#)

**Product Description :** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2") Cord Grip Body, Box only

**Series Number :** 130137

**Status :** Active

**Product Category :** Power Distribution

**Engineering Part Number :** 3059



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2") Cord Grip Body, Box only
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875075

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

### Physical

Cord Diameter	7.92-15.88mm (.312-.625")
Cord Grip Body Size	F4 1"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	Yes

Material - Housing	Rubber
Mounting Style	Portable
Net Weight	438.169/g
Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton
Receptacle Type	N/A

---

This document was generated on May 25, 2026