

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2451320805

Status:

Active

Overview:

Description:

Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 0.5m Length, 8 Circuits, Black

General	
Product Family	Cable Assemblies
Series	245132
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Overmolded	Yes
Overview	microfit_30
Product Name	Micro-Fit 3.0
Type	Overmolded Assembly
UPC	889056867221
Physical	
Cable Length	0.50m
Circuits (Loaded)	8
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	52.500/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.50mm
Wire Size AWG	20
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	3.5A
Voltage - Maximum	300V AC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	245132080-PK
Sales Drawing	2014400096-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

245132 Series

Mates With

Micro-Fit 3.0 Plug Housings 43020

Micro-Fit 3.0 Headers 43045

Micro-Fit 3.0 Test Plug 44242

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION