





RBF63X06C10C 2

(Part shown, no material (X) specified)

PN	Description
RB63-X06Y	(1) RB63X06Y, Top
RBF63X10Y	(1) RBF63X10Y, Bottom
8063	(1) RB63 O-Ring
6051	(4) #6-32 X 1" Captive PH Pan Hd Screw
6022	(4) #10 High/Low Pan Hd x 1/4"
6113	(4) #6-32 Threaded Insert

 =INTERIOR DIMENSIONS (@ BOTTOM)

2 =STANDARD COLORS (Y) ARE: BLACK (B), CLEAR (C) AND GRAY (G)
TOPS AND BOTTOMS ALL POSSIBLE COMBINATIONS AVAILABLE
STANDARD MATERIALS (X) IS: POLYCARBONATE (P)

- Watertight enclosure meets or exceed Nema 4 and or IP67.


DIMENSIONS in Inch
[mm]

ALL DIMENSIONS ARE $\pm .010"$ 5/9/2023
2009 Wright Ave., La Verne, CA. 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

SERPAC

Electronic Enclosures

RBF63 Circuit Board (Fits all Parts starting with RBF63)



(REFERENCE ONLY)