Straight Blade Devices

15 and 20 Ampere, 125 Volts

2 Pole, 3 Wire Grounding

HBL® Extra Heavy Duty Compact and Style Line® Decorator Receptacles

Fed.Spec.



15A 125V
NEMA 5-15R
UL CSA
0.5 HP




20A 125V
NEMA 5-20R
UL Listed
1 HP

Receptacles

HBL® Extra Heavy Duty Compact, Back and Side Wired, Duplex


Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired.	Black	**HBL5252BK**	**HBL5352BK**
	Blue	–	**HBL5352BL**
	Brown	**HBL5252**	**HBL5352**
	Gray	**HBL5252GY**	**HBL5352GY**
	Ivory	**HBL5252I**	**HBL5352I**
	Red	**HBL5252R**	**HBL5352R**
	White	**HBL5252W**	**HBL5352W**
On a 4 in. (101.6) round cover.	Brown	**HBL5253**	–



HBL5252

HBL® Extra Heavy Duty Compact, Side Wired Only, Duplex


Description	Color	Catalog Numbers	
Flush, nylon face, side wired only.	Brown	**HBL5242**	**HBL5342**
	Gray	**HBL5242GY**	**HBL5342GY**
	Ivory	**HBL5242I**	**HBL5342I**
	White	**HBL5242W**	**HBL5342W**
Ring terminal connection.	Brown	**HBL5242RT**	**HBL5342RT**



HBL5242

Heavy Duty, Single

Description	Color	Catalog Numbers	
Flush, side wired only.	Brown	**HBL5251**	–
	Ivory	**HBL5251I**	–
Panel mount 1.75 in. (44.5) centers.	Brown	**HBL5258**	**HBL5358**
	Ivory	**HBL5258I**	–




HBL5251


Heavy Duty Style Line® Decorator*

Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired.	Almond	**HBL2152AL**	**HBL2162AL**
	Black	**HBL2152BK**	**HBL2162BK**
	Brown	**HBL2152**	**HBL2162**
	Gray	**HBL2152GY**	**HBL2162GY**
	Ivory	**HBL2152I**	**HBL2162I**
	Office White	**HBL2152OW**	**HBL2162OW**
	White	**HBL2152WA**	**HBL2162WA**
Isolated ground.(1)	Gray	–	**IG2162GY**
	Orange	**IG2152**	**IG2162**

Notes: See page A-44 for accessories.
See Section K for wallplates.
(1) See Section J for complete line of isolated ground devices.
**Style Line Duplex devices are not Fed. Spec. Listed.*



HBL5258



HBL2152

Downloaded from Arrow.com.