

Catalog No. FBP-50

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			high speed
Rated current	I	A	50
Rated voltage			AC 700 V DC 700 V
Size			21 x 91 mm
Breaking Capacity		kA	200
Standard/Approval			UL
Shape			cylindrical with centre-bolted tags

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	50
Rated voltage		V	700
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

Additional product information (links)

Product datasheet (pdf)	http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-b/Bus_Ele_DS_720041_FBP-A.pdf
-------------------------	---