

4

3

2

1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
FB DIST
00


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	25JUN19	T.Q	W.H


KINKING FORMING
4 PLACES

SECT E-E

4 Pos.






NOTES:

1. MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS


SECT E-E

KINKING FORMING
4 PLACES

5 Pos.

3 Pos.
SECT E-E0.2X45°
CHAM
ø0.7KINKING FORMING
3 PLACESKINKING FORMING
2 PLACES2 Pos.
SECT E-ERECOMMENDABLE PCB LAYOUT
(PCB THK: 0.8-1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.2

Ø-PLC	±
1-PLC	±
2-PLC	±
3-PLC	±
4-PLC	±
ANGLES	±

MATERIAL

SEE NOTE

FINISH

, SEE NOTE

DWN 22JAN03

CHK S.XU

S.YAO 22JAN03

T. SASAKI 22JAN03

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
SHANGHAI, CHINAPOST HEADER ASS'Y POLARIZE TYPE (BOX-V TYPE)
(AMP CT CONNECTOR 2mm PITCH)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292131	

SCALE 5:1 SHEET 1 OF 2 REV A

