




C2G

**Discontinued - 3.3ft (1m) SC-SC 10Gb 50/125 OM3 Duplex Multimode Fiber Optic Cable (TAA Compliant) - Aqua**  
Part No. 11015



This OM3 Duplex Multimode Fiber Optic Cable is ideal for connecting 10GBase-SR, 10GBase-LRM, SFP+ and QSFP+ transceivers for 10 gigabit network connections. This cable meets all TIA/ANSI standards and the stringent TAA compliance requirements for anyone who needs to procure products exclusively manufactured in countries on the Trade Agreement Act list. This cable also provides backward compatibility with existing 50/125 equipment and the performance headroom required to support LED and VCSEL laser light sources, and 10 gigabit ethernet applications.

## Features & Benefits

Designed to support 10 gigabit network connections and equipment

Meets all TIA/ANSI standards

Backward compatibility with existing 50/125 equipment

## Specifications

### General Info

Product Line	C2G	Color	Aqua
UPC Number	757120110156	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

### Dimensions

Product Length US	3.3 FT	Cable Length	3.3 ft
-------------------	--------	--------------	--------

### Trade Programs

TAA Compliant	Yes
---------------	-----

### Technical Information

Fiber Optic Cable Type	Multimode, OM3	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	45 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Data Transfer Rate	10 Gbps	Connector 2	SC Male
Connector 1	SC Male	Fiber Size	50/125