



Pushing Performance
Since 1945

Han PP V14 SCRJ plug metal w/o SC



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 241 0402
Specification	Han PP V14 SCRJ plug metal w/o SC
HARTING eCatalogue	https://harting.com/09352410402

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	SCRJ
Element	Connector sets
Specification	AIDA compliant
Features	Intuitive locking mechanism

Version

Shielding	Unshielded
Number of contacts	2
Locking type	PushPull
Pack contents	incl. housing and SCRJ insert Without contacts

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	6.5 ... 9.5 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated



Pushing Performance
Since 1945

Material properties

Material (O-ring)	NBR
Material (cable seal)	TPE
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14) IEC 61754-24 Mating face
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	62.04 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140054394
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408