ADAM TECH



ANTENNAS


Downloaded from Arrow.com.

Adam Tech's RF Antennas are an optimal solution for any application transmitting or receiving electromagnetic waves. This series is headlined by WiFi, LTE, and GPS antennas, offered as either embedded or external. Designed with versatility in mind, they are available in a variety of lengths, mounting orientations, and specifications. Adam Tech is committed to providing reliable solutions to the wide world of wireless communication.



FEATURES AND BENEFITS:

- External and embedded antennas
- 5G, 4G, 3G, and 2G standards
- WiFi and LTE
- Navigation systems, such as GPS and Galileo
- Enable high speed wireless communication
- Variety of lengths
- Horizontal and vertical mounting orientations
- Wide range of frequencies



APPLICATIONS:

- Routers
- Navigation systems
- Radars
- Televisions
- Radios
- Mobile phones
- Automobiles
- Communication systems



The products displayed in this brochure represent the various types of Antennas Adam Tech has available. **Click here** to view Adam Tech's full Antenna product line.

Downloaded from Arrow.com.

ANT-19031EB78
External Magnetic Antenna



4G, 3G, 2G, NB-IoT, & CAT M1 Standards
Length: 185.00mm [7.28in]
Frequency Range: 824~960MHz or 1710~2690MHz

ANT-19036EB56
External Tilt Antenna, SMA Connection



ISM & LoRa Standards
Length: 109.00mm [4.29in]
Frequency: 868MHz

ANT-19073EB56
External Tilt Antenna, Flat, SMA Connection



5G, 4G, 3G, 2G, NB-IoT,
CAT M1, Wi-Fi, & BT Standards
Length: 152.40mm [6.00in]
Frequency Range: 600~6000MHz

ANT-20287EB56
External Low Profile Antenna, SMA Connection



3G, 2G, & NB-IoT Standards
Length: 51.50mm [2.03in]
Frequency Range: 698~960MHz or 1710~2170MHz

Downloaded from Arrow.com.

ANT-190071B77
RF Antenna, Flat Adhesive to U.FL



4G, 3G, 2G, NB-IoT, & CAT M1 Standards
Cable Length: 101.00mm [3.98in]
Antenna Length: 87.17mm [3.43in]
Frequency Range: 824~960MHz or 1710~2690MHz

ANT-190541B97
RF Antenna, Flat Adhesive to IPEX




3G & 2G Standards
Cable Length: 70.00mm [2.76in]
Antenna Length: 35.80mm [1.41in]
Frequency Range: 800~2100MHz

ANT-200051B66
SMD Antenna



GPS, L1/L5, GLONASS, & Galileo Standards
Dimensions: 26mm x 7.65mm x 3mm
Frequency: 1176.45/1575.42/1602.56MHz

ANT-20264IB93
GNSS Passive GPS Patch Antenna, Adhesive Type with Pin



GPS, GLONASS, Galileo,
& BeiDou Standards
Dimensions: 25mm x 25mm x 4mm
Frequency: 1575.42/1602/1608MHz

Downloaded from Arrow.com.

To contact us, scan the QR code to reach our website inquiry form.

adam-tech.com

Created: Jul-2022
Last Revised: Sep-2024

CONFIDENTIAL AND PROPRIETARY
© Adam Tech. All rights reserved. This document contains confidential and proprietary information belonging to Adam Tech. It is provided solely for design and reference purposes by authorized parties. Any reproduction, distribution, display, or disclosure to third parties, in whole or in part, without the prior written consent of Adam Tech, is strictly prohibited. Adam Tech retains all rights, including copyright, trademark, trade secret, and all other intellectual property rights worldwide.

Downloaded from Arrow.com.