
HellermannTyton

# Technical data sheet

## Article number:
## 116-01812 T18R




| | |
|---|---|
| **Product Group** | Cable ties polyamide 6.6 standard |
| **Product Family** | T-Series in PA66 coloured |
| **Material** | Polyamide 6.6 (PA66) |
| **Colour** | Red (RD) |

| | |
|---|---|
| **Application Tool** | EVOcut, MK7P, MK10-SB, MK20, EVO7i, EVO7iSP |
| **Bundle Ø max.** | 22.0 mm |
| **Bundle Ø min.** | 1.5 mm |
| **Flammability** | UL 94 V2 |
| **Halogen-free** | Yes |
| **Height (H)** | 3.7 mm |
| **Length (L)** | 100.0 mm |
| **Min.Tensile Strength** | 80 N |
| **Operating Temperature** | -40 °C to +85 °C |
| **Package Content** | 100 pcs. |
| **Package Content packed in** | pack |
| **Releasable Closure (Yes/No)** | No |
| **Thickness (T)** | 1.0 mm |
| **Toothing (Serration)** | Inside Serrated |
| **UV-Stabilised** | No |
| **Variant** | Inside Serrated |
| **Weight/Unit** | 0.00028 kg |
| **Width (W)** | 2.45 mm |

HF ✓ RoHS ✓

created on 18. September 2026, 6:06 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.