

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301910085

Status:

Active

Overview:

Lighting Accessories

Description:

Replacement Housing for 300 310

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

NEMA Configuration

Outlet

Overview

Product Name

Type

UPC

Portable Lighting

130191

N/A

N/A

Lighting Accessories

Woodhead

Accessory

78678861996

Physical

Cord Length - Primary

Cord Length - Secondary

Depth

Duty

Guard Included

Guard Type

Height

Length

Material - Guard

Packaging Type

Socket Construction

N/A

N/A

46.48mm (1.830")

Industrial

No

N/A

101.60mm (4.000")

140.97mm (5.550")

N/A

Carton

Assembled

Electrical

Bulb Type

Lamp Type

Lamp Wattage - Maximum

On/Off Switch

Voltage (Fixture) - Maximum

N/A

N/A

N/A

N/A

N/A

Material Info

Engineering Number

306

EU ELV

Not Reviewed

EU RoHS

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Reviewed

Not Reviewed

Search Parts in this Series

130191 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION