



Part Number : 1062250101

Product Description : MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 3.00mm, Multimode, 12 Fiber, Plenum, OM3, 3.0m Length, Aqua

Series Number : 106225

Status : Active

Product Category : Fiber Optic Cable Assemblies


Documents & Resources

Drawings

Drawing 1062250101_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106225
Description	MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 3.00mm, Multimode, 12 Fiber, Plenum, OM3, 3.0m Length, Aqua
Connector to Connector	MPO-to-MPO
Mode	Multimode
Product Name	MPO
UPC	191128897471

Physical

Boot Type	Straight
Cable Length	3.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	36.524/g
Single Ended	No
Wire/Cable Type	12 Fiber OM3 Plenum

This document was generated on Jul 21, 2024