





Stecklänge / mating length

E S L


0.8 ±0.1 0.8 ±0.1 4.8 ±0.2

E = early mate, late break / voreilend

S = standard


L = late mate, early break / nacheilend

Bestückungsplan / contact layout




Isolierwerkstoff / housing material : PBT GF 30
Bauart 4 / type 4
Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles
Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2
Lötanschluss 0,6x0,6mm / solder terminal 0,6x0,6mm

Leiterplatten-Lochbild / PCB drillhole pattern



Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16046 to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale 2:1				
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.				Designation Messerleiste C 32 Löt <i>Male Connector C32 solder</i>				
				b		26.11.2012				www.ERNI.com		374545
Index		Date						Class		STVC		A3

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.