



**C2G**  
**Discontinued - 9.8ft (3m) ST-ST 9/125 OS2 Duplex Single-Mode Fiber Optic Cable - Yellow**  
Part No. 11238



Cost-effective solution that provides high bandwidth and transmission rates over longer distances. This high quality fiber optic patch cable is specifically designed for gigabit ethernet applications. The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 9/125 Single-mode fiber, immune to electrical interference.

## Features & Benefits

Designed to support gigabit ethernet applications

Patented injection molding process for greater durability

Optically inspected and tested for insertion loss

Pull-proof jacket design, immune to electrical interference

## Specifications

### General Info

Product Line	C2G	Color	Yellow
UPC Number	757120112389	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		

### Dimensions

Product Length US	9.8 FT	Cable Length	9.8 ft
-------------------	--------	--------------	--------

### Technical Information

Fiber Optic Cable Type	OS2, Single-Mode	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	45 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Connector 2	ST Male	Connector 1	ST Male
Fiber Size	9/125		