Part number

M7APE 24.32



Surface mounting housing, E-Xtreme® V-TYPE series, with 2 levers, M32 cable entry, size 104.27, high construction

Product description	
Product type	Surface mounting housing
Series	E-Xtreme® V-TYPE
Closing type	With 2 levers
Size	Size 104.27
Cable entry	With cable entry M32
Specification	High construction
Technical data	
IP degree of protection	IP66 / IP67 / IP69
Further technical details	
Weight	495,00 g
Operating temperature range (min, max)	-40°C...+125°C


Material properties	
Other materials	Lever: Stainless steel Gasket: FKM
Colour	RAL 7016 grey
RoHs conformity	Compliant
China RoHs - EFUP	E
REACH SVHC substances	No
Approvals / Standards	
Certifications	CQC, DNV, BV
UL	ECBT2
cUL	ECBT8
General ordering information	
EAN13 code	8015747250498
eCl@ss 8.1	27440202
ETIM 7.0	EC000437
Packaging Information	
Packaging length	230,00 mm
Packaging height	160,00 mm
Packaging width	330,00 mm
Packaging weight	5,23 kg
Packaging volume	12,14 dm³
Packaging description	Carton box
Packaging quantity	10 Pcs
Packaging EAN code	8015747250610
Sub-packaging weight	2,62 kg
Sub-packaging description	Plastic packaging
Sub-packaging quantity	5 Pcs
Sub-packaging EAN barcode	8015747250627

Downloaded from Arrow.com.

Part number

M7APE 24.32

Catalogue drawings



type	A	B	C	D	E	F
M7P 24	63	45	57	169	132	144
M7AP 24	80	45	57	169	132	144

Notes

Dimensions shown in mm are not binding and may be changed without notice.

Downloaded from Arrow.com.