

Cable binder base - WT-BASE LS HF 4 - 3240706

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable binder base, for cable binders up to 4 mm wide, self-adhesive (rubber) and screwable, 4 mm fixing hole, 4-sided cable binder feed-through



RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 046356 703932
GTIN	4046356703932
Weight per Piece (excluding packing)	0.712 g
Custom tariff number	39269097
Country of origin	Croatia

Technical data

Dimensions

Length (b)	19 mm
Width (a)	19 mm
Height (c)	5 mm
Hole diameter	4.1 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (assembly)	-15 °C ... 40 °C

General

Color	transparent
-------	-------------

Cable binder base - WT-BASE LS HF 4 - 3240706

Technical data

General

Type	Fixing
Components	free from silicone and halogen
Material	ABS
Flammability rating according to UL 94	HB
Tensile strength	220 N

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	23159007
eCl@ss 11.0	23152509
eCl@ss 4.0	27140700
eCl@ss 4.1	27140700
eCl@ss 5.0	27140700
eCl@ss 5.1	27140700
eCl@ss 6.0	27140700
eCl@ss 7.0	23159007
eCl@ss 9.0	23159007

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 6.0	EC000449
ETIM 7.0	EC000449

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703
UNSPSC 19.0	39121731

