



Quality Products. Service Excellence.

Server Rack Cabinet *C4RR Series*

UL 2416 Rated 3,000 lbs Weight Capacity



When you need cabinets quickly, our pre-assembled C4RR are a great option. Based off of our most popular requested configurations, each cabinet is factory configured and is packaged ready-to-ship. Click [here](#) to view our C4 Series' components.

Features

- Constructed in:
 - 14-gauge steel (body)
 - 16-gauge steel (doors and side panels)
 - 10-gauge steel (tapped mounting rails)
 - 12-gauge steel (square hole mounting rails)
- EIA-310-D compliant 10-32 tapped or square hole punched rails with rack unit labels.
- Zinc-plated mounting rails provide superior surface areas for equipment grounding.
- The 30" wide C4 rails have cable-tie support and pass-through holes.
- The 24" wide C4 includes:
 - Generous cabling space
 - Four (4) 3.5" wide cable entry holes on the top
- The 30" wide C4 includes:
 - Extra generous cabling space
 - Support for up to four optional 4" deep vertical cable managers
- Vertical cable trays are available for both 24" and 30" width cabinets
- Vertical cable managers feature magnetic latching doors, and 3.5" wide x 4" deep cable space and are available for 30" width cabinets

Specifications

- UL Listed 2416 rated for up to 3,000 lbs (1,360 kg) static load rating.
- Infinite-depth setting using C-channel struts.
- Zinc-plated mounting rails provide superior surface areas for equipment grounding.
- Four (4) leveling feet are included with support for optional casters.
- Grounding studs provided on frame as well as side panels and doors.
- Finished in textured black powder paint. Additional colours available upon request.
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.

Included Components

- All configurations include:
 - One (1) Welded C4 Cabinet Frame with Top Cable Entry Holes
 - Two (2) Removable Side Panels (with 1/4 turn latches)
 - Four (4) Leveling Feet
 - Eight (8) Keys
 - Starter pack of (50) 10-32 Screws and cage nuts.
- **C4RR Data Cabinet Specific Components include:**
 - Two (2) Pairs infinitely adjustable square hole rails
 - One (1) Plexi Front Door

- One (1) Perforated Rear Door
 - One (1) Four (4) Fan cutout Top Panel
 - One (1) Vertical Cable Tray with Toolless PDU Mounting
- **C4RR Server Cabinet Specific Components include:**
 - Two (2) Pairs infinitely adjustable square hole rails
 - One (1) Perforated Front Door
 - One (1) Split Perforated Rear Door
 - One (1) Four (4) Fan cutout Top Panel
 - Two (2) Vertical Cable Trays with Toolless PDU Mounting

Accessories

- Cabinet Fan Tops
- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Rack Unit Label
- Adjustable Depth Cable Manager
- Horizontal Ring Cable Manager
- Horizontal Finger Cable Manager
- Cable Management Arm
- Mounting Hardware
- Rack Panels
- Outlet Strips
- Side Panel Locking Kit
- Four Post Mounting Sliding Shelf
- Adjustable Depth Shelf
- Sliding Keyboard Shelf
- Horizontal Lacing Strip
- Horizontal Hinged Cable Manager
- Horizontal Steel Finger Cable Manager
- Vertical Cable Tray
- Vertical Cable Manager with Door
- Grounding
- Caster Set

C4RR Data Cabinet

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
C4RR247331DBK1	80.08	24.00	31.50	42U	73.50	19.00	29.50
C4RR247336DBK1	80.08	24.00	36.00	42U	73.50	19.00	34.00
C4RR247342DBK1	80.08	24.00	42.00	42U	73.50	19.00	40.00
C4RR247731DBK1	83.58	24.00	31.50	44U	77.00	19.00	29.50
C4RR247736DBK1	83.58	24.00	36.00	44U	77.00	19.00	34.00
C4RR247742DBK1	83.58	24.00	42.00	44U	77.00	19.00	40.00
C4RR307731DBK1	83.58	30.00	31.50	44U	77.00	19.00	29.50
C4RR307736DBK1	83.58	30.00	36.00	44U	77.00	19.00	34.00
C4RR307742DBK1	83.58	30.00	42.00	44U	77.00	19.00	40.00

Overall height includes leveling feet.

C4RR Server Cabinet

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
C4RR247331SBK1	78.00	24.00	31.50	42U	73.50	19.00	29.50
C4RR247336SBK1	78.00	24.00	36.00	42U	73.50	19.00	34.00
C4RR247342SBK1	78.00	24.00	42.00	42U	73.50	19.00	40.00
C4RR247731SBK1	83.75	24.00	31.50	44U	77.00	19.00	29.50
C4RR247736SBK1	83.75	24.00	36.00	44U	77.00	19.00	34.00
C4RR247742SBK1	83.75	24.00	42.00	44U	77.00	19.00	40.00
C4RR307731SBK1	83.75	30.00	31.50	44U	77.00	19.00	29.50
C4RR307736SBK1	83.75	30.00	36.00	44U	77.00	19.00	34.00
C4RR307742SBK1	83.75	30.00	42.00	44U	77.00	19.00	40.00

Overall height includes leveling feet.

7/27/2018

Server Rack Cabinet (C4RR Series) - Hammond Mfg.

Tags: **Server Rack Enclosure Cabinet, Rack Enclosure, Network Shelter, Net Shelter**

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.