








THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA			SCALE FULL
OPERATING FORCE - - - - - 6-12 LB		CONTACT ARRANGEMENT 			DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE - - - - - 30 LB MAX		2X S P D T			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
RELEASE FORCE - - - - - 4 LB MIN		28 VDC			
PRETRAVEL - - - - - .040 MAX		LOAD	SEA LEVEL	50,000 FT.	ONE PLACE (.0) ±.030
DIFFERENTIAL TRAVEL - - - - - .020 MAX		RES	1.0		TWO PLACE (.00) ±.015
OVERTRAVEL - - - - - .250 MIN		IND	0.5		THREE PLACE (.000) ±.005
					ANGLES ±
					WEIGHT

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 6 - GOLD CONTACT BASIC SWITCHES