


REV.	DATE	ECR NO.	DESCRIPTION
NC	10/16/09	XXXXXX	INITIAL RELEASE



CENTER CONTACT TO ACCEPT 0.022 TO 0.042 PIN [0.056 TO 0.107]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE	Amphenol Connex			
					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm		DRAWN M.ZHANG		10/16/09				
6	LOCK RING	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"		CHECKED			PART DESCRIPTION			
5	GASKET	SILICONE	RED	1			ISSUED			F PANEL JACK			
4	INSULATOR	PTFE	NATURAL	1	DO NOT SCALE DRAWING		SHEET 1 OF 1			PART NO.			
3	CONTACT PIN	BRASS	BRIGHT TIN	1			CAD FILE			222146			
2	INSULATOR	PTFE	NATURAL	1			C:/CONNEX/222146.DWG			DWG. NO. 222146.DWG			
1	BODY	BRASS	NICKEL	1						REV. NC			
DESCRIPTION					MATERIAL		FINISH		QTY	SIZE A			
										SCALE NA			