



Part Number : 1301020190

Series Number : 130102

Product Category : Lamps and Lights

Product Description : Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, 15.24m (50.0') 16-/3 SOOW

Status : New Business Not Supported

Engineering Number : 115IB163

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Lamps and Lights

Series	130102
Description	Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard with Reflector, 15.24m (50.0') 16-/3 SOOW
NEMA Configuration	NEMA 5-15
Product Family	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678804591

Electrical

Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Insulated, Open End, Reflector
Height	371.35mm (14.620")
Lamp Type	A23
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton