

6

5

4

3

2

1

D

D

C




C

B

B

A

A

**NOTES:**

1. MATERIAL AND FINISHES:
CONTACT: PRECISION MACHINED COPPER ALLOY, 1.27 μ [.000050] GOLD OVER NICKEL PLATE.
2. CONTACT IS COMPLIANT TO THE CURRENT RoHS DIRECTIVE.
3. DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY D-SUB PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.

BY SM		CHK ND		3RD ANGLE 		POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART. Positronic® CONNECTPOSITRONIC.COM	
APR PA		RELEASED DATE: 2021-03-03		SCALE NTS			
TOLERANCES ±0.03mm [.001 INCHES]FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES]FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES]FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES]FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]							
PART NUMBER MC6020D/AA-15				SERIES RD			
TITLE MC6020D/AA-15							
CREATED ON: 2021-02-14				SHEET SHEET 1 OF 1		REV A	

6

5

4

3

2

1