

Part Number : [936000350](#)

Product Description : Heavy-Duty Plastic Gable Gland with Gasket, M20x1.5 Thread, Black RAL 9005

Series Number : 93600

Status : Active

Product Category : Heavy-Duty Cable Glands


Engineering Part Number : 7000.7823.1



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Plastic Gable Gland with Gasket, M20x1.5 Thread, Black RAL 9005
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	DIN EN 50262, EN 60529
UPC	887191852225

Physical

Cable Diameter	6.00-12.00mm
Gland Color	Black RAL 9005
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Packaging Type	Bag
Panel Cutout Diameter	20.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	M20x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Use with Part(s)

Description	Part Number
-------------	-------------

Use With

Sealed Enclosures and Boxes

This document was generated on May 27, 2026