Part Number : 2219512112
Product Description : Pre-Crimped Lead Female CP Terminal-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 0.75mm² Wire, Black
Series Number : 221951
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2219512112_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	221951
Description	Pre-Crimped Lead Female CP Terminal-to-Pigtail, Tin (Sn) Plating, 150.00mm Length, 0.75mm^2 Wire, Black
Application	Automotive, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CP Crimp Terminals
Product Name	CP Terminal
UPC	198282671596

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	250V AC

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.154/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire/Cable Type	FLRYW
Wire Size mm^2	0.75

Downloaded from Arrow.com.