


Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/15	


APPROVED: _____

DATE: _____ TITLE: _____









RECOMMENDED P.C.B LAYOUT

SPECIFICATIONS:
Material:
Housing: PPA, rated UL94V-0, Color: Brown
Contact: Phosphor Bronze T=0.2mm
Plating:
Gold flash over Nickel underplate overall
Electrical:
Contact resistance: 30 Milliohms max
Insulation resistance: 1000 Mega ohms min
Dielectric Voltage: 500V AC one sec level
Temperature Rating:
Operating temperature: -25°C to +85°C.
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	5/27/15
CHECKED	OC	5/27/15
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
BATTERY COIN CELL HOLDER

SIZE	PART NO.	REV.
X	BH-44A-5	-

REF: S00136C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.