




Technical Data:	
Case Material	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop during Resistive Load	150mV
Voltage	to 32VDC
Duty Rating	400A
Overload	1200A-4min
	1600A-1.5min
	2000A-10sec
Sealing	IP 67/ IEC 529
Vibration	4G / 50-2000Hz
Shock G-Level	6G / 11ms
Weight	360g / 0.8 Pound
Temperature Range	-40°C to +85°C
Wire Section (at nominal Load)	min. 240mm²
Switch Lever	not removeable
Max. Torque (Main Contacts)	15-20Nm