

SUVTXR2B6S

 [Printer Friendly](#)

- Computer and Peripheral (5)
- Home UPS (2)
- Network and Server
 - > Smart-UPS
 - > Smart-UPS On-Line
 - > Symmetra
- Data Center and Facility 3 Phase (14)
- UPS Management (7)

Standard Lead Time: Usually Ships within 2 Weeks



★★★★★

Be the first to [write a review](#)

[+ More Images](#)

[Return to Uninterruptible Power Supply \(UPS\)](#)

Technical Specifications

Product Overview

Documentation

Options

Ratings and Reviews

Nominal Input Voltage	208V 3PH, 400V 3PH
-----------------------	--------------------

Battery Volt-Amp-Hour Capacity	5530
--------------------------------	------

Battery Type	VRLA
Battery mounting	Enclosed battery cabinet
Battery manufacturer	--
Expected Battery Life (years)	3 - 5
Included Battery Modules	2
Available Battery Slots	4
Battery Placement	External Frame
Battery blocks per string	32

Net Weight	399.55 KG
Maximum Height	1499.00 mm
Maximum Width	523.00 mm
Maximum Depth	925.00 mm
Shipping Weight	430.45 KG
Shipping Width	650.00 mm
Shipping Height	1643.00 mm
Shipping Depth	1062.00 mm
Color	Black

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-999.9 meters
Storage Temperature	-50 - 40 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

Regulatory Approvals	C-tick,CE,ISO 14001,ISO 9001
Standard Warranty	1 year repair or replace