

Han 16HP-HTE-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 39 016 0426
Specification	Han 16HP-HTE-M25
HARTING eCatalogue	https://b2b.harting.com/19390160426

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HP
Type of hood/housing	Hood

Version

Size	16 B
Version	Top entry
Cable entry	1x M25
Locking type	Screw locking
Field of application	Hoods/housings for rough environments

Technical characteristics

Tightening torque (screw locking)	3 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP66
	IP68
	IP69 / IPX9K acc. to ISO 20653

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel



Pushing Performance

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
CE	Yes

Commercial data

Packaging size	1
Net weight	295 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors