
Data sheet

WQV 50N/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, Silver grey, 150 A, Number of poles: 4, Pitch in mm (P): 18.50, Insulated: No, Width: 9.5 mm
Order No.	1834080000
Type	WQV 50N/4
GTIN (EAN)	4032248379873
Qty.	5 items

Downloaded from Arrow.com.

Data sheet

WQV 50N/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	65.5 mm	Height (inches)	2.5787 inch
Width	9.5 mm	Width (inches)	0.374 inch
Net weight	63.9 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	tinned copper	Colour	Silver grey

System specifications

Version	For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	18.50 mm

General

Number of poles	4	Installation advice	Direct mounting

Rating data

Rated voltage	400 V	Nominal current	150 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Downloaded from Arrow.com.