

Part Number : [391002503](#)


Product Description : 15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 3 Circuits

Series Number : 39100

Status : Active

Product Category : Terminal Blocks and Barrier Strip

Engineering Part Number : M800-04-03-5-M1



Documents and Resources

Drawings

[391002503_sd.pdf](#)

3D Models and Design Files


[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:e4149c83-9ee8-4b45-87cb-b57b3af49127
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39100
Description	15.00mm Pitch, Beau Eurostyle Two-Screw Terminal Strips, 3 Circuits
Application	Wire-to-Wire
Component Type	One Piece
Keyword	Terminal Strip
Product Name	Eurostyle Two Screw
Type	Terminal Strips
UPC	78172545259

Electrical

Current - Maximum per Contact	63.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	White
Entry Angle	Horizontal

Lock to Mating Part	No
Material - Metal	Stainless Steel, Steel
Material - Resin	Nylon
Net Weight	23.500/g
Number of Rows	2
Orientation	Vertical
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Screw
Wire Size (AWG)	6, 8, 10, 12, 14
Wire Size mm ²	2.00-13.50

This document was generated on May 13, 2026