
HellermannTyton

Technical data sheet

Article number:
115-06202 RT40R



Product Group	Releaseble Cable Ties
Product Family	RT Series With Extended Pawl
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

Bundle Ø max.	51.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Length (L)	215.9 mm
Min.Tensile Strength	180 N
Operating Temperature	-40 °C to +85 °C
Package Content	1000 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	Yes
Specifications	UL-ZODZ2.E64139
UL-File Number	E64139
UV-Stabilised	Yes
Variant	Inside Serrated
Width (W)	4.0 mm

RoHS

created on 18. September 2026, 7:19 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.