

Product data sheet

Specifications



Galaxy VX 750kVA 480V Remote Maintenance Bypass Cabinet

GVXMBCR750KG

Overview

Presentation	Maintenance bypass cabinet which can be installed remotely and isolates the UPS during service operations.
Lead time	Special Order - Call for Quoted Lead Times

Main

Range of product	Galaxy VX
Range compatibility	Galaxy VX

Physical

Colour	Black
Height	197 cm
Width	80 cm
Depth	90 cm
Net weight	280 kg

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	99 cm
Package 1 Weight	300 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Take-back	No

Image of product / Alternate images

Alternative



