



Part Number : [351500292](#)

Product Description : VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red

Series Number : 35150

Status : Active

Product Category : Connector Accessories



Documents and Resources

Drawings

[351500292_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)


[PK-35150-002-001.pdf](#)

[PS-35150-001-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	35150
Description	VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red
Component Type	Terminal Position Assurance (TPA)
Product Name	VersaBlade
UPC	800754375450

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Red
Lock to Mating Part	Yes

Material - Resin	Nylon
Net Weight	0.253/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural	<u>351500200</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Blue	<u>351500204</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable	<u>351500209</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Natural	<u>351500210</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Blue	<u>351500214</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable	<u>351500219</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural	<u>351500400</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Blue	<u>351500404</u>
VersaBlade Hybrid Receptacle	<u>351500409</u>

Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural	<u>351500410</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Red	<u>351500412</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue	<u>351500414</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>351500419</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Yellow, Glow-Wire Capable	<u>351503209</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Yellow, Glow-Wire Capable	<u>351503219</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Blue, Glow-Wire Capable	<u>351504209</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Blue, Glow-Wire Capable	<u>351504219</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 4 Circuits, Blue, Glow-Wire Capable	<u>351504419</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural	<u>351510210</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Blue	<u>351510214</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510219</u>
VersaBlade Hybrid Plug Housing,	<u>351510410</u>

4 Circuits, Positive Lock, Natural	
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue	<u>351510414</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510419</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Red, Glow-Wire Capable	<u>351512219</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>351513219</u>
VersaBlade Hybrid Plug Housing, 2 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514219</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514419</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u>2026500909</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

This document was generated on May 08, 2026