Datasheet for part number MKJ1A6W13-37PA

Our Catalog Part Number: MKJ1A6W13-37PA
Our Global Manufacturing Part Number: 155124-1001
Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ1

Product Datasheet	
Series	Threaded Coupling, Double Start ACME Thread
Class	Environmental Plug and Receptacle with Banding/Overmolding Attachment
Shell Style	Straight Plug
Plating	Aluminum/OD Cad
Contact Arrangement	13-37
Contact Quantity	37
Contact Size	Size 23
Contact Gender	Pin, Crimp, Removable
Insulator Resistance	5000 Megaohms Minimum
Wire Accommodation	#22 - #28 AWG
Current Rating	5 Amps Maximum
Voltage Rating	500 VAC RMS Sea Level
Operating Temperature	-65°/+175°
Contact Resistance	8 Milliohms Maximum
Vibration Resistance	37 g′ in Accordance with MIL-STD-1344 Method 2005, Condition IV
Physical Shock	300 g in Accordance with MIL-STD-1344 Method 2004, Condition E
EMI Shielding Effectiveness	55-75 Min. dB Attenuation
Frequency	100 MHz to 1000 MHz

Specifications and dimensions subject to change.

Downloaded from Arrow.com.