


.062" PITCH COMPLIANT PIN HD Stacker™



GSTB universal stacking connector
For top, middle, and bottom-of-stack


MATES WITH GSTB, GSTB (.095), GSTF, GSTT, GSTBL



- **Innovative Chevron Contact System (CCS)**
- **High-density layouts from 40 to 300 contacts**
- **Polarized insulators**
- **Keyed guide pin hardware for mis-mate protection**






All Glenair HD Stacker™ connectors are equipped with our innovative .062" pitch high-density Chevron Contact System (CCS). Special non-orthogonal socket tines enable both higher density layouts as well as improved signal integrity. The GSTB is equipped with pin/socket contacts with solder-free press-fit board mounting.



The GSTB is a universal stacking connector that may be used in the bottom, middle, or top position depending on application. Shown: GSTB stack-mating with GSTB.

How to Order GSTB HD Stackers					
Sample Part Number	GSTB	-120	-.270	-G	1
Series	GSTB = Standard Profile Stacker				
Number of Contacts	40, 80, 120, 160, 200, 240, 300				
Pin Termination Length	.270, .300, .350, .400, .500, .600, .700, .800, .900, 1.000				
Hardware	G Keyed Guide Pin / Guide Socket* T Keyed Guide Pin / Female #2-56 Jackpost for GSTT mate F Keyed Guide Socket / Fixed (non-rotating) Male Jackscrew for GSTF mate <i>Use .270 termination length only</i>				
Key Position	1*	2	3	4	

* Choose Hardware/Key Position -G1 for best availability / fastest delivery



Number of Contacts	A		B	
	in	mm	in	mm
40	0.90	22.86	0.70	17.78
80	1.40	35.56	1.20	30.48
120	1.90	48.26	1.70	43.18
160	2.40	60.96	2.20	55.88
200	2.90	73.66	2.70	68.58
240	3.40	86.36	3.20	81.28
300	4.15	105.41	3.95	100.33