


REV.	DATE	DESCRIPTION
NC	02/12/07	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
7						DRAWN	G.R.S.	02/12/07											
6						CHECKED			PART DESCRIPTION 1.0/2.3 RECEPTACLE PC MOUNT BULKHEAD EDGECARD										
5	SPANNER NUT	BRASS	GOLD	1		ISSUED													
4	LOCK WASHER	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 282123–75										
3	CONTACT PIN	BER. COPPER	GOLD	1															
2	INSULATOR	TEFLON	NATURAL	1			CAD FILE		DWG. NO. 282123–75.DWG					REV.	NC	SIZE	A	SCALE	NA
1	BODY	BRASS	GOLD	1			C:/282/282123–75.DWG												
	DESCRIPTION	MATERIAL	FINISH	QTY															