



Part Number : [734152380](#)

Product Description : MCX Plug, Right-Angle,
Solder, RG-405 (.086" Semi-Rigid) Cable, Brass Body,
Tin (Sn) Plated, 50 Ohms

Series Number : 73366

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734152380 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Plug, Right-Angle, Solder, RG-405 (.086" Semi-Rigid) Cable, Brass Body, Tin (Sn) Plated, 50 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	800756039299

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Plug
Keying to Mating Part	N/A
Net Weight	1.130/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No

Wire/Cable Type	RG-405, .086" Semi-Rigid Coaxial
-----------------	----------------------------------

This document was generated on Sep 22, 2025