
Data sheet

# MF-W 5/5 MINI MC NE GN

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.
We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

| | |
|---|---|
| Version | MultiFit, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00 WAGO, Legrand, Entrelec, green |
| Order No. | 1924290000 |
| Type | MF-W 5/5 MINI MC NE GN |
| GTIN (EAN) | 4032248563289 |
| Qty. | 500 items |



Downloaded from Arrow.com.

# Data sheet

## MF-W 5/5 MINI MC NE GN

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Height | 5 mm | Height (inches) | 0.1968 inch |
| Width | 5 mm | Width (inches) | 0.1968 inch |
| Net weight | 0.15 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -40…100 °C |

### Environmental Product Compliance

| | | |
|---|---|---|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | No SVHC above 0.1 wt% | |
| Product Carbon Footprint | Cradle to gate | 0.001 kg CO2 eq. |

### General data

| | | |
|---|---|---|
| Material colour according to resistance code | 5 | |
| Type of printing | neutral | |
| Width | 5 mm | |
| UL 94 flammability rating | V-2 | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | green | |
| Halogen | No | |
| Basic material | Polyamide 66 | |
| Printed characters | neutral | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| compatible printer | PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2 | |
| Number of markers per combination | 1 MultiCard = Terminal marker | |
| Operating temperature range | -40…100 °C | |
| Application/manufacturer | WAGO, Legrand, Entrelec | |

### Connector markers

| | |
|---|---|
| Pitch in mm (P) | 5.00 mm |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |




Downloaded from Arrow.com.

# MF-W 5/5 MINI MC NE GN

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings



### Drawing





Downloaded from Arrow.com.