



+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
SMA R/A PLG DS RG402 PSS
Subminiature Coax | SMA

2-1478905-0
TE Internal Number: 2-1478905-0

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

Connector Interface SMA
Connector Style Plug
Mated Outer Diameter (Approximate) 6.35 mm [.25 in]
Cable Type RG 402
Sealable No

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

SMA RIGHT ANGLE PLUG DIRECT SOLDER CAPTIVE CONTACT RG402/U

PDF (TIFF AVAILABLE)

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA
Connector Style Plug
Sealable No
Connector & Contact Terminates To Wire & Cable

Body Features

Cable Connector Orientation Right Angle
Body Material Stainless Steel
Body Finish Passivated
Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold
Center Contact Material Brass
Connector Product Type Connector Assembly
RF Connector Contact Configuration Not Captivated

Termination Features

Termination Method to Wire & Cable Solder

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]
Length 16.51 mm [.65 in]
Flats Dimension 8.0 A/F

Usage Conditions

Cable Type RG 402

Packaging Features

Packaging Method Box
Packaging Quantity 100

Other

Dielectric Material PTFE
Gasket Material Silicone Rubber
Coupling Nut Plating Finish Passivated
Coupling Nut Material Stainless Steel
Grade Professional

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance

PDF

