



Pushing Performance
Since 1945

har-switch momentary 2x 45°



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 2205
Specification	har-switch momentary 2x 45°
HARTING eCatalogue	https://b2b.harting.com/09454532205

Identification

Category	Operator interfaces
Series	har-switch
Element	Selector switches
Specification	Momentary 2x 45°

Version

Diameter of the mounting hole	30.5 mm
Details	This item requires additional contact blocks and a module holder to be functional. Please select these under "Matching Products".

Technical characteristics

Actuation path	6 mm
Overvoltage category	III (protection by low voltage)
Tightening torque	≤2.5 Nm Fixing nut
Operating temperature	-40 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP65
Isolation group	I (600 ≤ CTI)
Thickness of the panel	1 ... 8 mm

Material properties

Colour	anthracite
--------	------------



Pushing Performance
Since 1945

Specifications and approvals

Specifications	EN 60947-5-1
UL / CSA	UL 60947-5-1 NKCR.E534795 CSA C22.2 No. 60947-5-1:22 NKCR7.E534795

Commercial data

Packaging size	10
Net weight	28.6 g
Country of origin	Germany
European customs tariff number	85365080
GTIN	5713140449701
ETIM	EC000222

Switching position

