



GD1826, Mech Ground, 2 Cables to Rod or Pipe

By Burndy

Catalog # [GD1826](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol) - 2/0 AWG (Str), 2" Rod, 2" Pipe.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	2 in
Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Rod Size	2 in
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0

Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size B Range	2
Conductor - Copper Tube Std Size Range	2
Conductor - Copper Tube Std Size	2

Dimensions

Package Height	0.000 in
Dimension - Height mm	111.3 mm
Dimension - Height inch	4.38 in
Dimension - Height fraction	4-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	3-3/4 in
Dimension - Width mm	94 mm
Dimension - Width inch	3.69 in
Dimension - B Length inch	1.31 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810238943
Type	GD
U Bolt Type	256
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810238943
UPC 14 Digit GTIN	00781810238943

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand