molex



**Part Number :** 1301460023
**Product Description :** Watertite Extreme Plug, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Black, Silicone Husk
**Series Number :** 130146
**Status :** Active
**Product Category :** Wiring Devices
**Engineering Part Number :** 14W33BLK

## Documents and Resources

### Drawings

1301460023_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Wiring Devices |
| Series | 130146 |
| Description | Watertite Extreme Plug, 2 Pole/3 Wire, NEMA 5-20, 125V, Cord Grip Body Size F2, Black, Silicone Husk |
| IP Rating | IP69K |
| NEMA Configuration | NEMA 5-20 |
| Product Name | Watertite Extreme |
| Specialty | N/A |
| Type | Plug |
| UPC | 78678871046 |

### Agency

| | |
|---|---|
| CSA | LR6837 |
| UL | E10176 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Cord Grip Body Size | F2 1/2" |

Downloaded from Arrow.com.

| | |
|---|---|
| Cord Type | N/A |
| Flange | No |
| Flip Lid | No |
| Gender | Male |
| Length | N/A |
| Lighted Connector | No |
| Locking Blade | No |
| Net Weight | 125.000/g |
| Poles | 2-pole/3-wire |
| Receptacle Type | N/A |



Downloaded from Arrow.com.