



Part Number : 190670100

Product Description : NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/8" (M16)

Series Number : 19067

Status : Planned for Obsolescence

Product Category : Ring and Spade Terminals

Engineering Number : G-977-58

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Planned for Obsolescence
Category	Ring and Spade Terminals
Series	19067

Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 2 AWG Wire, Stud Size 5/8" (M16)
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066830

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/8" (M16)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	15.24mm max.
Wire Size (AWG)	2

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	<u>640013900</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

This document was generated on Jul 28, 2024