








PC board drilling dimensions
(after plating - thickness: 1.60 to 3.20 mm)



ROHS PART NUMBER

PART NUMBER	
Flash gold	D50P91C4GL00LF
0.76µ gold	D50P91C6GL00LF

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0001

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family D-SUB	
ltr	ecp no	dr	date	tolerances unless otherwise specified		scale 2:1	title	
G	ELX-I-21654	AB	2015-10-26	angles	linear		MALE DELTA-D 50 STRAIGHT PRESS-FIT	
H	ELX-I-24020	AAB	2016-06-06	0°±2°				
				dr	PESSON	1995-10-03	dwg no	sheet 1 of 1
				engr	MITHUN PAUL	2016-06-06	C01-8646-0377	
				chr	ATHUL A.B	2016-06-06	A3	
				appd	BIJU K PAUL	2016-06-06	type Product Customer Drawing	
sheet index	revision	H						
	sheet	1						