



**Part Number :** 1301080125  
**Product Description :** Super-Safeway 13W  
Fluorescent Hand Lamp with Cord Ballast  
Location and Switch, Cord Type 18/3 SJTOOW,  
Cord Length 15.24m (50.0')  
**Series Number :** 130108  
**Status :** Active  
**Product Category :** Lamps and Lights  
**Engineering Number :** 1085-3



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130108
Description	Super-Safeway 13W Fluorescent Hand Lamp with Cord Ballast Location and Switch, Cord Type 18/3 SJTOOW, Cord Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678861272

## Electrical

Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Fluorescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	18/3 SJTOOW
Depth	38.10mm (1.500")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	66.04mm (2.600")
Lamp Type	PL13/41
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Net Weight	1.000/g
Outlet	None
Packaging Type	Carton

---

---

This document was generated on Apr 26, 2025