

- 
- Products
- Industry Solutions
- CAREERS
- Resources

- Find Distributor
- Contact Molex



ANVIL 5040520098



Series image - Reference only

Status: Active
Series: [578116](#)
Category: Molex Parts

Product Environmental Compliance

EU ELV:Not Reviewed

EU RoHS:Not Reviewed

EU RoHS Phthalates:Not Reviewed

China RoHS:Not Reviewed

REACH SVHC:Not Reviewed

Low-Halogen Status:Not Reviewed

Part Detail

General

Status	Active
Category	Molex Parts
Series	578116
UPC	887191090870

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products

- Antennas
- Application Tooling
- Cable Assemblies
- Connected Lighting
- Connectors
- Copper Flex
- Electrical Products
- Industrial Automation
- Membrane Switches
- Optical Solutions
- Printed Electronic Solutions

Quick Links

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Industries](#)
- [Literature](#)
- [Molex Racing](#)
- [Press Room / Press Releases](#)
- [Product Index](#)
- [Sitemap](#)

Resources

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | [Feedback](#)
- Jobs
- Legal | [Trade Shows](#)
- Mobile Site
- Supplier Portal
- Privacy Policy
- Tradeshow

Stay Connected



Molex.com would like to place cookies on your computer to help us make this website better.

To find out more about the cookies, see our [Privacy Policy](#). To accept cookies from this site, please click the 'I Accept' button.

I Accept

I Decline

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered to their respective owners.

© Copyright 2017