


1

2


3

4


5



MATING PART
3230-XX-0101-00




MATING PART
3230-XX-0102-00



Specifications:
Current rating:1.0A
Voltage rating:50V AC,DC
Contact resistance:20m ohm Max
Insulation resistance:1,000M ohm Min
Withstanding voltage:500V AC/minute
Operating Temperature:-40°C ~ +105°C

Materials:
Insulator:Nylon9T (UL94V-0)
Standard Color:Black
Contact:Brass
Plating:Gold Plated Over Nickel

Circuits	DIM		Circuits	DIM	
	A	B		A	B
6	2.54	18.16	34	20.32	35.94
8	3.81	19.43	40	24.13	39.75
10	5.08	20.70	44	26.67	42.29
16	8.89	24.51	50	30.48	46.10
20	11.43	27.05	60	36.83	52.45
26	15.24	30.86	68	41.91	57.53
30	17.78	33.40			



RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X=±0.20
.XX=±0.15

CHECKED:


UNIT: MM

SCALE:1:1

APPROVAL:

SHEET: 1 / 1

PROJECTION:



CnC Tech

Industrial Cable and Connector Technology

DESCRIPTION:

1.27mm Shrouded Header R/A Type

PART NO:

3210-XX-002-12-00

SIZE

A4

REV A 05-FEB-2020

FILE

BY