




 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 2:1	RJ45 fieldpatchcable, overmolded, 4xAWG 22, IP20, 2x RJ45 plug				
			Detail.	23.10.06	MR						
			Insp.	23.10.06	RA						
			Stand.								
DRS480A	11.03.09	MS					TB 09 45 771 xxxx				Blatt/ page 1/2
34083	10.05.07	MS	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP								
33689											
Mod.	Dat.	Name				Sub.	Sub				

1				2				3				4				5				6				7				8			
Cont. no.	Part-No.			Type of cable								Dim. a[m]			cont. no.	Part-No.			Type of cable								Dim. a[m]				
A	1	09 45 771 0021			RJI cable, 4xAWG 22/1, solid, CAT5								0,5 m			51	09 45 771 1165			RJI cable, 4xAWG 22/7, trailing, CAT5								2 m			
	2	09 45 771 0022			RJI cable, 4xAWG 22/1, solid, CAT5								1 m			52	09 45 771 1166			RJI cable, 4xAWG 22/7, trailing, CAT5								3 m			
	3	09 45 771 0023			RJI cable, 4xAWG 22/1, solid, CAT5								1,5 m			53	09 45 771 1167			RJI cable, 4xAWG 22/7, trailing, CAT5								4 m			
	4	09 45 771 0024			RJI cable, 4xAWG 22/1, solid, CAT5								2 m			54	09 45 771 1168			RJI cable, 4xAWG 22/7, trailing, CAT5								5 m			
	5	09 45 771 0025			RJI cable, 4xAWG 22/1, solid, CAT5								3 m			55	09 45 771 1169			RJI cable, 4xAWG 22/7, trailing, CAT5								6 m			
	6	09 45 771 0026			RJI cable, 4xAWG 22/1, solid, CAT5								4 m			56	09 45 771 1170			RJI cable, 4xAWG 22/7, trailing, CAT5								7 m			
	7	09 45 771 0027			RJI cable, 4xAWG 22/1, solid, CAT5								5 m			57	09 45 771 1171			RJI cable, 4xAWG 22/7, trailing, CAT5								8 m			
	8	09 45 771 0028			RJI cable, 4xAWG 22/1, solid, CAT5								6 m			58	09 45 771 1172			RJI cable, 4xAWG 22/7, trailing, CAT5								9 m			
B	9	09 45 771 0029			RJI cable, 4xAWG 22/1, solid, CAT5								7 m			59	09 45 771 1173			RJI cable, 4xAWG 22/7, trailing, CAT5								10 m			
	10	09 45 771 0030			RJI cable, 4xAWG 22/1, solid, CAT5								8 m			60	09 45 771 1174			RJI cable, 4xAWG 22/7, trailing, CAT5								15 m			
	11	09 45 771 0031			RJI cable, 4xAWG 22/1, solid, CAT5								9 m			61	09 45 771 1175			RJI cable, 4xAWG 22/7, trailing, CAT5								20 m			
	12	09 45 771 0051			RJI cable, 4xAWG 22/1, solid, CAT5								10 m			62	09 45 771 1176			RJI cable, 4xAWG 22/7, trailing, CAT5								30 m			
	13	09 45 771 0052			RJI cable, 4xAWG 22/1, solid, CAT5								15 m			63	09 45 771 1177			RJI cable, 4xAWG 22/7, trailing, CAT5								40 m			
	14	09 45 771 0053			RJI cable, 4xAWG 22/1, solid, CAT5								20 m			64	09 45 771 1178			RJI cable, 4xAWG 22/7, trailing, CAT5								50 m			
	15	09 45 771 0054			RJI cable, 4xAWG 22/1, solid, CAT5								30 m			65	09 45 771 1179			RJI cable, 4xAWG 22/7, trailing, CAT5								60 m			
	16	09 45 771 0055			RJI cable, 4xAWG 22/1, solid, CAT5								40 m			66	09 45 771 1180			RJI cable, 4xAWG 22/7, trailing, CAT5								70 m			
	17	09 45 771 0056			RJI cable, 4xAWG 22/1, solid, CAT5								50 m			67	09 45 771 1181			RJI cable, 4xAWG 22/7, trailing, CAT5								80 m			
	18	09 45 771 0057			RJI cable, 4xAWG 22/1, solid, CAT5								60 m			68	09 45 771 1182			RJI cable, 4xAWG 22/7, trailing, CAT5								90 m			
	19	09 45 771 0058			RJI cable, 4xAWG 22/1, solid, CAT5								70 m			69	09 45 771 1183			RJI cable, 4xAWG 22/7, trailing, CAT5								100 m			
	20	09 45 771 0059			RJI cable, 4xAWG 22/1, solid, CAT5								80 m																		
	21	09 45 771 0060			RJI cable, 4xAWG 22/1, solid, CAT5								90 m																		
	22	09 45 771 0061			RJI cable, 4xAWG 22/1, solid, CAT5								100 m																		
	23	09 45 771 1134			RJI cable, 4xAWG 22/7, stranded, CAT5								0,3 m																		
	24	09 45 771 1121			RJI cable, 4xAWG 22/7, stranded, CAT5								0,5 m																		
	25	09 45 771 1122			RJI cable, 4xAWG 22/7, stranded, CAT5								1 m																		
	26	09 45 771 1123			RJI cable, 4xAWG 22/7, stranded, CAT5								1,5 m																		
	27	09 45 771 1124			RJI cable, 4xAWG 22/7, stranded, CAT5								2 m																		
	28	09 45 771 1125			RJI cable, 4xAWG 22/7, stranded, CAT5								3 m																		
D	29	09 45 771 1126			RJI cable, 4xAWG 22/7, stranded, CAT5								4 m																		
	30	09 45 771 1127			RJI cable, 4xAWG 22/7, stranded, CAT5								5 m																		
	31	09 45 771 1128			RJI cable, 4xAWG 22/7, stranded, CAT5								6 m																		
	32	09 45 771 1129			RJI cable, 4xAWG 22/7, stranded, CAT5								7 m																		
	33	09 45 771 1130			RJI cable, 4xAWG 22/7, stranded, CAT5								8 m																		
	34	09 45 771 1131			RJI cable, 4xAWG 22/7, stranded, CAT5								9 m																		
	35	09 45 771 1151			RJI cable, 4xAWG 22/7, stranded, CAT5								10 m																		
	36	09 45 771 1132			RJI cable, 4xAWG 22/7, stranded, CAT5								13 m																		
	37	09 45 771 1152			RJI cable, 4xAWG 22/7, stranded, CAT5								15 m																		
	38	09 45 771 1153			RJI cable, 4xAWG 22/7, stranded, CAT5								20 m																		
	39	09 45 771 1154			RJI cable, 4xAWG 22/7, stranded, CAT5								30 m																		
	40	09 45 771 1155			RJI cable, 4xAWG 22/7, stranded, CAT5								40 m																		
	41	09 45 771 1156			RJI cable, 4xAWG 22/7, stranded, CAT5								50 m																		
	42	09 45 771 1157			RJI cable, 4xAWG 22/7, stranded, CAT5								60 m																		
	43	09 45 771 1158			RJI cable, 4xAWG 22/7, stranded, CAT5								70 m																		
	44	09 45 771 1159			RJI cable, 4xAWG 22/7, stranded, CAT5								80 m																		
	45	09 45 771 1160			RJI cable, 4xAWG 22/7, stranded, CAT5								90 m																		
	46	09 45 771 1161			RJI cable, 4xAWG 22/7, stranded, CAT5								100 m																		
	47	09 45 771 1184			RJI cable, 4xAWG 22/7, trailing, CAT5								0,3 m																		
	48	09 45 771 1162			RJI cable, 4xAWG 22/7, trailing, CAT5								0,5 m																		
F	49	09 45 771 1163			RJI cable, 4xAWG 22/7, trailing, CAT5								1 m																		
	50	09 45 771 1164			RJI cable, 4xAWG 22/7, trailing, CAT5								1,5 m																		

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße/Free size tolerances											
						Dat.			Name			Maßstab/Scale 2:1			RJI fieldpatchcable, overmolded, 4xAWG 22, IP20, 2x RJ45 plug					
						Detail.			23.10.06									MR		
						Insp.			23.10.06									RA		
DRS480A			11.03.09			MS			Stand.											
34083			10.05.07			MS			HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP						TB 09 45 771 xxxx			Blatt/ page 2/2		
33689																				
Mod.			Dat.			Name														